


Retrofitting **WRAPS**



Before removing old fluorescent or LED lamps,
shut off power to the light.

* Retrofitting should be done by a qualified installer who will follow all relevant building and electrical codes.



Retrofitting **WRAPS**




Remove lens.

Retrofitting **WRAPS**




Remove lamps.

Retrofitting **WRAPS**



Remove ballast cover.




Disconnect power wires and carefully remove old ballast and sockets.



Housing is ready for the installation of the
BLU DRiVe™ BD35.




Choose between 750mA (35W), 600mA (28W), or 450mA (21W). After splicing building power through the disconnect provided, plug in the 24 inch white BB cable to port BB-1 on the BD35 BLU DRiVe™.



Overview of BLU DRiVe™ features.

Retrofitting **WRAPS**

24" cable and antenna



Plug 24 inch BLU BaRsTM cable into the BLU DRiVeTM BB (1) port and leave opposite end outside of ballast cover for connection to BLU BaRTM.
Leave 3 inches of Antenna outside of metal housing.
Replace cover when complete.

Retrofitting **WRAPS**




Plug 15 inch cable into one end of first BLU Bar™. Plug 24" cable into opposite end and then place BLU Bar™ on the housing.
Plug the open end of the 15 inch cable into the second BLU Bar™ and then place on housing.



Tuck excess connector cable into the housing and leave 3 inches of antenna out

Use a portable drill with Philips head to drill one tek screw
(provided with BLU BaRs™) into both sides of each BLU Bar™ .
Replace lens.




Retrofitting **WRAPS**



You are now ready to energize! The BLU BaRs™ will express the default color and power settings.



Retrofitting **WRAPS**



After energizing you may connect and program using the SMART BLU™ App. See **www.smartblu.com** for more information.

Download the SMART BLU™ App





Retrofitting **WRAPS**




Using the SMART BLU™ app, you may adjust color from 2700K...

Download the SMART BLU™ App





Retrofitting **WRAPS**



...to 6500K and any color in between.


Download the SMART BLU™ App



SMART
BLU™



Retrofitting **WRAPS**



You may also dim from 100% down to 1%
and anywhere in between.

Download the SMART BLU™ App



SMART
BLU™